


General accessories

Article


Article no.



Mounting console

34-3535200103

made of thermoplastic polyester
incl. mounting material (screws and dowels)
and holding elements



Bluetooth board

34-35252080

for upgrading EcoAdd pumps
for data exchange via Bluetooth



Adapter cable

for connecting existing EMP pump connections when
replacing EMP pumps with Eco pumps.

Adapter cable, control input, EMP – EcoAdd

34-35252082

Adapter cable, output, EMP – EcoAdd

34-35252083



Oval gear meter

for volumetric measurement of the rate of flow

Ordering data are to be found in chapter
„Measuring and Controlling, OGM PLUS“



Signal horn with integrated red flash light

34-35418271053

230 V / 50 Hz / IP 33 RO

Hose connection material

Article

Article no.

Hose connection sets 12/21 mm

Connection set Di12/Da21-G11/4-PP-GY

34-35249238

Connection set Di12/Da21-G11/4-PVDF-NA

34-35249258

Suction lances

Article

Article no.



Suction lances with reserve and empty signal report

incl. of ball non-return valve, suction strainer, zero-potential empty signal contact (empty = contact interrupted)

Tube diameter: 32 mm
Hose connection: 12/21 mm
Connection cable: circular connector
Turn-on voltage: max.50 V AC/DC
Switching current: 0.5 A
Rupturing capacity: 10 W / 10 VA

SGL VCPVFPEPGL000 G5/8-10-2SS-0475-99-07 (for container 20 l) 34-35186157


SGL VCPVFPEPGL000 G5/8-10-2SS-0725-99-07 (for container 30/60 l) 34-35186158

SGL VCPVFPEPGL000 G5/8-10-2SS-0975-99-07 for container 100/200 l) 34-35186159


SGL VCPVFPEPGL000 G5/8-10-2SS-1125-99-07 (for container 200 l) 34-35186160

Suction lance code see next page!

Suction lance code



5.4.3 Bottom admission valve



Article

- BSV VC PV FP GL 000 G 1¼ – 07
- BSV VC PV EP GL 000 G 1¼ – 07
- BSV VA VA FP VA 000 G 1¼ – 99
- BSV VA VA EP VA 000 G 1¼ – 99

Article no.



- 34-35249019
- 34-35249025
- 34-35249036
- on request

Hose connection: bush for hose NW 16 mm and NW 19 mm

- BSV VC PV FP GL 000 G 1¼ – XX
- BSV VC PV EP GL 000 G 1¼ – XX

- 34-35249017
- 34-35249030

Metering valves



Article

Article no.

DVO PV PV FP GL 008 G 1¼ – G 1¼ – 07	34-35249026
DVO PV PV EP GL 008 G 1¼ – G 1¼ – 07	34-35249027
DVO PV PV FP GL 008 G 1¼ – G 1¼ – 99	34-35249086
DVO PV PV EP GL 008 G 1¼ – G 1¼ – 99	on request
Metering pipe PP G ¾ for DVO G 1¼	34-35249235
Metering pipe PV G ¾ for DVO G 1¼	34-35249236

Suction and pressure lines

Suction and pressure lines

available by the metre
max. operating pressure: 15 bar (at 20° C)



PVC-fabric, 12/21 mm (int.Ø/ext.Ø)	34-35417400127
PVC-fabric, 19/27 mm (int.Ø/ext.Ø)	34-35417400131

Note:


We explicitly point out that PVC fabric tubes have a limited lifetime if alkaline chemicals will be used. To avoid damage for your staff and your company the tubes have to be exchanged at least every 6 months. In case of non-compliance we exclude all kinds of liability and responsibility.



PE-X tube 12/16 mm, coiled bundle 50 m	34-35417400362
---	----------------



	PP	PVDF
Threaded connection G1/2"a – PEX 12/16	34-35415102357	34-35415101970



	PP	PVDF
Screw on connection G1 1/4"i - PEX 8/12	34-35250093	34-35250075
Screw on connection G1 1/4"i - PEX 12/16	34-35250099	34-35250076



	PVDF
T-Union PVDF - PEX 12/16	34-35415102303